




AFTvision 机器视觉实验及测试台架







一、AFT-BR400 型机器视觉实验及测试台架 (单位: mm)

			
		AFT-EB400 测试台架仪器箱 长宽高: 64*40.5*21(mm)	
底板: AFT-BR401	立杆: AFT-BR402	微调旋钮升降架: AFT-BR403	立杆固定底座: AFT-BR404
			
长宽厚: 400×350×10	30×25×600	长宽高: 215×115×93, 微调: +60~ -6	长宽高: 75×48×40


二、AFT-BR300 型机器视觉实验及测试台架 (单位: mm)

			
		AFT-EB300 测试台架仪器箱 长宽高: 60*40.5*21(mm)	
		AFT-EB301 测试台架仪器箱 长宽高: 49*40.5*21(mm)	
台架: AFT-BR301	台架: AFT-BR302	台架: AFT-BR303	微调旋钮升降架: AFT-BR304/305
			
底板: 385×265×30 立杆: Φ25×290, 多个可叠加	底板: 265×385×30 立杆: Φ25×290, 多个可叠加	底板: 385×265×30 立杆: Φ25×290, 多个可叠加	外形: 210×120×95, 微调范围: +60~ -18;
相机支杆 BR305: Φ9.9×200		转换块 BR306: 60×40×25, 大孔: Φ25, 小孔: Φ10;	
		BR306:  BR307: 	

三、AFT-BR200 型机器视觉实验及测试台架 (单位: mm)

AFT-BR200	AFT-BR201	AFT-BR202	微调旋钮升降架: AFT-BR203/204
			
底板: 300×200×80 立杆: Φ21×250 可多个叠加	底板: 300×200×80, 立杆: Φ21×250, 可多个叠加	底板 225×155×30 立杆: Φ21×250 可多个叠加	长宽高: 150×45×100 微调范围: +25~ -25
相机支杆 BR205: Φ9.9×200 转换块 BR206: 60×40×25 大孔: Φ22, 小孔: Φ10			BR205:  BR206: 

四、AFT-BR20 型机器视觉光源支架 (单位: mm)

AFT-BR20 型光源支架	光源支架套件	AFT-BR21 型相机支架	相机支架套件
			
1、底座 BR22: 60×60×40; 2、立杆 BR23: Φ15×375; 3、转换块 BR24: 115×22×20, 大孔: Φ15, 小孔: Φ10; 4、相机支杆 BR25: Φ9.9×200; 5、光源固定架 BR26: 234×200, Φ9.9			

五、可选配套附件 (单位: mm)

二维平移台: AFT-BR100	垂直升降台: AFT-BR101	相机小支架: AFT-BR102	水平刻度横杆 AFT-BR103	全方位相机支架 AFT-BR104	磁性底座支架 AFT-BR105
					
180×155×34 X 平移: 74, Y 平移: 55	长宽高: 100×80×65 微调范围: 30	立杆高: 218, 底座: Φ85, 杆长: 300	长宽高: 300×50×7	大支架: Φ85X218, 小支 架: Φ57X83	

说明: 根据使用要求不同, 客户选择的可能只是以上列表中的一部分, 并不是全部。